





修 订	标 记	修 改 描 要	签 名	日 期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
AO		NEW DWG		2016-03-12





P.C.B. LAYOUT

TABLE:

P位	Dimension mm	
	A	B
2P	1.25	7.65
3P	2.54	8.90
4P	3.75	10.15
5P	5.00	11.30
6P	6.25	12.65
7P	7.50	13.90
8P	8.75	15.15
9P	10.00	16.40
10P	11.25	17.65
11P	12.50	18.90
12P	13.75	20.15
13P	15.00	21.40
14P	16.25	22.65
15P	17.50	23.90
16P	23.75	30.15



NOTE:
 Current rating:1A AC,DC
 Voltage rating:125V AC,DC
 Temperature range:-25℃~+85℃
 Insulation resistance:100MΩ/Min
 Withstanding voltage:500V AC/minute
 Contact resistance:20mΩ/Max
 PIN:Brass/Gold-Plated
 Suitable With:A1254HF Series Housing



深圳市华德共创科技有限公司
 Shenzhen Huade co-create Technology Co.,LTD
 电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: 1.25MM Pitch 90° Wafer	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC1254WR-S-XP
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	SCALE
			UNIT
			CODE NUMBER
		2014-06-18	1:1
			mm
			A001