






STRUCTURE (构造)				
NO.	ITEM (项目)	SPECIFICATION (规格)		
1	INSULATION (胶膜)	印字膜: 通用版20624 (43μm)		
		白膜: 80° C 60V (43μm)		
2	SUPPORTING TAPE (补强板)	225μm	Blue (蓝色)	
3	CONDUCTOR (导体)	Thickness (厚度)	0.035	±0.005
		Width (宽度)	0.65	±0.03
4	CONDUCTOR (导体镀层)	PLATED (电镀)	锡Sn (1μm)	MIN
		PLATED (电镀)		

DIMENSION (尺寸)			
No. of conductors (导体数目)	N	(N) P	
Pitch (间距)	P	1.0	±0.06
Span (总间距)	SP	(N-1)*1	±0.1
Width (总宽度)	W	(N+1)*1	±0.12
Margin (边缘宽度)	M	1.0	±0.12
Total length (总长度)	TL	(TL)	±2.0
Insert Thickness (插接端厚度)	T	0.3	±0.05
Surface Thickness (线身厚度)	ST	0.12	±0.03
Strip Length (裸铜长度)	S1	4.0 4/3可定做	±0.5
	S2	4.0 4/3可定做	±0.5
Supporting Tape Length (补强板长度)	B1	6.0 8/6/5/4/可定做	±1.0
	B2	6.0 8/6/5/4/可定做	±1.0

技术要求:

- 1、保存环境: 温度15~25℃ 湿 度: 30~50RH%
- 2、保质期: 镀金: 12个月 镀锡: 6个月
- 3、产品符合ROHS 2.0标准

DESIGN:	Xiping Huang				广东国连电子有限公司 GUANGDONG GUOLIAN ELECTRONICS CO.,LTD			
CHECK:	Ke Tian							
APPROVED:	Youquan Xu			TITLE: FFC CABLE A型				
DIM	TOL	DIM	TOL					
X.	±0.25			PART NO. 1. 0*NP*TL*A (4/4/5/5) (0.035*0.65)				
X. X	±0.20							
X. XX	±0.15							
X. XXX								
				REV. A	SCALE: N/A	UNIT: mm	SHEET: 1/1	