






| 修订<br>REV | 标记<br>MARK | 修改摘要<br>REVISION DESCRIPTION | 签名<br>SIGNATURE | 日期<br>DATE |
|-----------|------------|------------------------------|-----------------|------------|
| A0        |            | NEW RELEASE                  | 黄艳兰             | 2021-05-09 |



### Specifications:

Contact resistance:  $\leq 20\text{m}\Omega$   
 Insulation resistance:  $\geq 100\text{M}\Omega$   
 Rated voltage: 50V AC DC  
 Rated current: 1.0A AC DC  
 Withstand Voltage: 500V AC/minute  
 Temperature Range:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$   
 Housing: PA6T UL94V-0, Natural (Beige)  
 Contacts: Phosphor bronze/Matte Sn  
 Solder Tabs: Phosphor bronze/Matte Sn



| Circuits | Dimensions (mm) |       |       |       | Circuits | Dimensions (mm) |       |       |       |
|----------|-----------------|-------|-------|-------|----------|-----------------|-------|-------|-------|
|          | A               | B     | C     | D     |          | A               | B     | C     | D     |
| 02       | 1.00            | 4.80  | 3.10  | 2.50  | *17      | 16.00           | 19.80 | 18.10 | 17.50 |
| 03       | 2.00            | 5.80  | 4.10  | 3.50  | *18      | 17.00           | 20.80 | 19.10 | 18.50 |
| 04       | 3.00            | 6.80  | 5.10  | 4.50  | *19      | 18.00           | 21.80 | 20.10 | 19.50 |
| 05       | 4.00            | 7.80  | 6.10  | 5.50  | *20      | 19.00           | 22.80 | 21.10 | 20.50 |
| 06       | 5.00            | 8.80  | 7.10  | 6.50  | *21      | 20.00           | 23.80 | 22.10 | 21.50 |
| 07       | 6.00            | 9.80  | 8.10  | 7.50  | *22      | 21.00           | 24.80 | 23.10 | 22.50 |
| 08       | 7.00            | 10.80 | 9.10  | 8.50  | *23      | 22.00           | 25.80 | 24.10 | 23.50 |
| *09      | 8.00            | 11.80 | 10.10 | 9.50  | *24      | 23.00           | 26.80 | 25.10 | 24.50 |
| *10      | 9.00            | 12.80 | 11.10 | 10.50 | *25      | 24.00           | 27.80 | 26.10 | 25.50 |
| *11      | 10.00           | 13.80 | 12.10 | 11.50 | *26      | 25.00           | 28.80 | 27.10 | 26.50 |
| *12      | 11.00           | 14.80 | 13.10 | 12.50 | *27      | 26.00           | 29.80 | 28.10 | 27.50 |
| *13      | 12.00           | 15.80 | 14.10 | 13.50 | *28      | 27.00           | 30.80 | 29.10 | 28.50 |
| *14      | 13.00           | 16.80 | 15.10 | 14.50 | *29      | 28.00           | 31.80 | 30.10 | 29.50 |
| *15      | 14.00           | 17.80 | 16.10 | 15.50 | *30      | 29.00           | 32.80 | 31.10 | 30.50 |
| *16      | 15.00           | 18.80 | 17.10 | 16.50 |          |                 |       |       |       |


**深圳市华德共创科技有限公司**  
 Shenzhen Huade co-create Technology Co., LTD  
 TEL : 0755-27111225 FAX : 0755-29940187

| -TOLERANCES-<br>UNLESS OTHERWISE SPECIFIED<br>公差参数表 |       |        |     | TITLE:<br>产品名称: SHLP1.0卧贴 |                                   |       |      |
|-----------------------------------------------------|-------|--------|-----|---------------------------|-----------------------------------|-------|------|
| X.X                                                 | ±0.30 | X.X°   | ±3° | APPD:<br>核准: 谢亮           | PART NO:<br>产品编号: HDGC1006WR-S-XP |       |      |
| X.XX                                                | ±0.30 | X.XX°  | ±2° | CHECK:<br>校对: 王建业         | DATE                              | SCALE | UNIT |
| X.XXX                                               | ±0.10 | X.XXX° | ±1° | DRAW:<br>绘图: 黄艳兰          | 2021-05-09                        | 1:1   | mm   |
|                                                     |       |        |     | CODE NUMBER<br>A018       |                                   |       |      |