

修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW RELEASE	黄艳兰	2019-12-10

Specifications:

Poles:02~04P
Contact resistance: $\leq 10\text{m}\Omega$
Insulation resistance: $\geq 1000\text{M}\Omega$
Rated voltage:600V AC DC
Rated current:1.0A AC DC
Withstand Voltage: 1800V AC/minute
Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
Housing:PA9T UL94V-0,Natural
Contacts:Brass/Sn-plated
Solder Tabs:Brass/Sn-plated

PIN	DIM A	DIM B	DIM C
2	10.00	4.00	6.65
3	14.00	8.00	10.65
4	18.00	12.00	14.65



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

TEL : 0755-27111216 FAX : 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: 4.00卧贴			
X.X	± 0.30	X.X°	$\pm 3^{\circ}$	APPD: 核准: 谢亮	PART NO: 产品编号: HDGC4002WR-S-XP		
X.XX	± 0.30	X.XX°	$\pm 2^{\circ}$	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX	± 0.10	X.XXX°	$\pm 1^{\circ}$	DRAW: 绘图: 黄艳兰	2019-12-10	1:1	mm
				CODE NUMBER A018			

PCB LAYOUT(Tolerance: ± 0.05)