



P/N	PIN	DIM. A	DIM. B
HMT-254WV-2x3P	2*3	5.08	7.62
HMT-254WV-2x4P	2*4	7.62	10.16
HMT-254WV-2x5P	2*5	10.16	12.70
HMT-254WV-2x6P	2*6	12.70	15.24
HMT-254WV-2x7P	2*7	15.24	17.78
HMT-254WV-2x8P	2*8	17.78	20.32
HMT-254WV-2x9P	2*9	20.32	22.86
HMT-254WV-2x10P	2*10	22.86	25.40
HMT-254WV-2x12P	2*12	27.94	30.48
HMT-254WV-2x13P	2*13	30.48	33.02
HMT-254WV-2x14P	2*14	33.02	35.56
HMT-254WV-2x15P	2*15	35.56	38.10
HMT-254WV-2x16P	2*16	38.10	40.64
HMT-254WV-2x17P	2*17	40.64	43.18
HMT-254WV-2x18P	2*18	43.18	45.72
HMT-254WV-2x20P	2*20	48.26	50.80
HMT-254WV-2x22P	2*22	53.34	55.88
HMT-254WV-2x25P	2*25	60.96	63.50
HMT-254WV-2x30P	2*30	73.66	76.20
HMT-254WV-2x32P	2*32	78.74	81.28

GENERAL TOLERANCES UNLESS SPECIFIED		 <b>深圳市华明通电子有限公司</b> Shenzhen Huamingtong Electronics Co., Ltd	
X. ±0.30	X.° ±5°	PART NO. HMT-254WV-2xNP	TITLE: 2.54DC3-NP in H8.9 180度 PC3.2 L11.5 6T
.X ±0.25	.X° ±1°	DESIGN: James	CUSTOMER
.XX ±0.20	.XX° ±0.5°	CHED: Talen	
MANUFACTURE DWG		APPD: Sophia	SCALE N:A
		 UNITS MM SHEET 1/1	