





REV.	DESCRIPTION	ECN NO.	NAME	DATE

SPECIFICATIONS
Current Rating: 1.0 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
AM-PM1.27-V11-2*1P	1	0.00	1.27
AM-PM1.27-V11-2*2P	2	1.27	2.54
AM-PM1.27-V11-2*3P	3	2.54	3.81
AM-PM1.27-V11-2*4P	4	3.81	5.08
AM-PM1.27-V11-2*5P	5	5.08	6.35
AM-PM1.27-V11-2*6P	6	6.35	7.62
AM-PM1.27-V11-2*7P	7	7.62	8.89
AM-PM1.27-V11-2*8P	8	8.89	10.16
AM-PM1.27-V11-2*9P	9	10.16	11.43
.....			
AM-PM1.27-V11-2*50P	50	(PIN-1)x1.27	(PIN)x1.27

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN® 	
DIM.	TOL.	TITLE: 1.27FH H4.3 2xnPin 180度 W3.0 U型 PC2.4 6T					
x.	±0.30						
x.x	±0.20						
x.xx	±0.10						
GENERAL ANGLE:		DWG. NO.: AM-PM1.27-V11-2*NP		CHECKED: MAX			
x.°	±5°	PART NO.: AM-PM1.27-V11-2*NP		DRAWN: ELLA			
x.x°	±1°						
x.xx°	±0.5°						
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL

RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)