







		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	



技术要求:

1. 塑件材料: PA66 (UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 20\text{m}\Omega$
4. 绝缘电阻: $\geq 1000\text{M}\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 3.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim +85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235 \pm 5^{\circ}\text{C}$, 时间 $2.5 \pm 0.5\text{s}$
10. 铅和镉等六大有害物质含量要符合环保要求。

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. .x ±0.25 .xx ±0.12 .xxx ±0.05 GENERAL ANGLE: x.* ±3°		TITLE: 压接式连接器						
		DWG. NO.: AF-VH3.96-NPZZ-W1			CHECKED: MAX			
		PART NO.: AF-VH3.96-NPZZ-W1			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	