REV.	DESCRIPTION	ECN NO.	NAME	DATE











Part No	Pin	A	B	C
AF-PH2.0-2PJK-W1	2	2.00	5.70	4.50
AF-PH2.0-3PJK-W1	3	4.00	7.70	6.50
AF-PH2.0-4PJK-W1	4	6.00	9.70	8.50
AF-PH2.0-5PJK-W1	5	8.00	11.70	10.50
AF-PH2.0-6PJK-W1	6	10.00	13.70	12.50
AF-PH2.0-7PJK-W1	7	12.00	15.70	14.50
AF-PH2.0-8PJK-W1	8	14.00	17.70	16.50
AF-PH2.0-9PJK-W1	9	16.00	19.70	18.50
AF-PH2.0-10PJK-W1	10	18.00	21.70	20.50
AF-PH2.0-11PJK-W1	11	20.00	23.70	22.50
AF-PH2.0-12PJK-W1	12	22.00	25.70	24.50
AF-PH2.0-13PJK-W1	13	24.00	27.70	26.50
AF-PH2.0-14PJK-W1	14	26.00	29.70	28.50
AF-PH2.0-15PJK-W1	15	28.00	31.70	30.50
AF-PH2.0-16PJK-W1	16	30.00	33.70	32.50

技术要求Specification:

1、材质Material: PA66 UL94V-0;

2、额定电流 Current rating:2.0A AC,DC

3、额定电压 Voltage rating:100V AC,DC

4、温度范围 Temperature range:-25℃to+85℃

5、接触电阻 Contact resistance:≤20mΩ

6、绝缘电阻Insulation resistance:≥1000MΩ

7、耐压Withstand voltage:800V AC/minute

8、塑件表面平整光洁，无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象.
Plastic surface smooth and clean, no obvious burrs, bubbles.distortion, gate strain, lack of material and other undesirable phenomena.

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		BXCONN®
DIM.	TOL.	TITLE: PH2.0MM HOUSING		
.x	±0.30			
.xx	±0.20			
.xxx	±0.10			
GENERAL ANGLE:				
x.°	±1°	DWG. NO.: AF-PH2.0-NPJK-W1	CHECKED: MAX	
		PART NO.: AF-PH2.0-NPJK-W1	DRAWN: ELLA	
		UNIT: mm / SCALE: none / SHEET: 1of 1 / DWG. SIZE: A4 / LAYER: bxconn	APPROVED: WILL	

BXCONN®