










技术指标:

- 1.额定电流:0.5A
- 2.温度范围:-40~85℃
- 3.额定电压:50V,AC/DC (等效)
- 4.接触电阻:≤0.03Ω
- 5.绝缘电阻:≥500MΩ

Part No	Pin	A	B	C
BX-0.5FPC-2H-QF4P	4	1.50	2.60	6.40
BX-0.5FPC-2H-QF5P	5	2.00	3.10	6.90
BX-0.5FPC-2H-QF6P	6	2.50	3.60	7.40
BX-0.5FPC-2H-QF7P	7	3.00	4.10	7.90
BX-0.5FPC-2H-QF8P	8	3.50	4.60	8.40
BX-0.5FPC-2H-QF9P	9	4.00	5.10	8.90
BX-0.5FPC-2H-QF10P	10	4.50	5.60	9.40
BX-0.5FPC-2H-QF11P	11	5.00	6.10	9.90
BX-0.5FPC-2H-QF12P	12	5.50	6.60	10.40
BX-0.5FPC-2H-QF13P	13	6.00	7.10	10.90
BX-0.5FPC-2H-QF14P	14	6.50	7.60	11.40
BX-0.5FPC-2H-QF15P	15	7.00	8.10	11.90
.....		...		
BX-0.5FPC-2H-QF61P	60	(61-1)*0.5	(61+1)*0.5+0.1	(61+7)*0.5+0.9

序号	品名	材质
1	端子	磷青铜/表面镀锡
2	焊片	黄铜/表面镀锡
3	基座	LCP UL94V-0 本色
4	锁条	LCP UL94V-0 黑色

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE

GENERAL TOLERANCE	
X.±0.15	±1°
.X±0.10	
.XX±0.05	

制图 DRAWING	EMMA
审核 CHECK	EVA
核准 APPROVAL	JADE
单位 UNITS	MM
比例 SCALE	1:1

料号 PART NO.	BX-0.5FPC-2H-QFNP	版本 REV.	A
品名 TITLE	0.5-B翻盖(H:2.0)	页次 SHEET	1/1
客户料号 CUTM.NO.			