REV.	DESCRIPTION	ECN NO.	NAME	DATE



SPECIFICATIONS
Current Rating: 1.0 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)





P/N	PIN	DIM.A	DIM.B
AM-PM2.54-V11-1*1P	1	0.00	1.27
AM-PM2.54-V11-1*2P	2	1.27	2.54
AM-PM2.54-V11-1*3P	3	2.54	3.81
AM-PM2.54-V11-1*4P	4	3.81	5.08
AM-PM2.54-V11-1*5P	5	5.08	6.35
AM-PM2.54-V11-1*6P	6	6.35	7.62
AM-PM2.54-V11-1*7P	7	7.62	8.89
AM-PM2.54-V11-1*8P	8	8.89	10.16
AM-PM2.54-V11-1*9P	9	10.16	11.43
.....	.....	.....	.....
AM-PM2.54-V11-1*50P	50	(PIN-1)x1.27	(PIN)x1.27



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

GENERAL TOLERANCE DIM. TOL. x. ±0.30 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: x.° ±5° x.x° ±1° x.xx° ±0.5°	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN®
	TITLE: 1.27FH H4.3 1xNPin 180度 W2.1 U型 PC2.4 6T					
	DWG. NO.: AM-PM2.54-V11-1*NP				CHECKED: MAX	
	PART NO.: AM-PM2.54-V11-1*NP				DRAWN: ELLA	
	UNIT: mm	SCALE: none	SHEET: 1of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL

WWW.BXCONN.COM 东莞市宝讯精密技术有限公司 ARTICLE: BX-CN-001-A