





SECTION A-A



- 技术要求:
- 1) 材质: 见附表;
 - 2) 电镀: 见附表;
 - 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
 - 4) 端子表面无氧化、电镀无不良现象。

温度范围: -25°C~85°C
额定电压: 30V AC/DC
额定电流: 0.5A AC/DC
接触电阻: ≤0.02Ω
绝缘电阻: ≥100MΩ
耐 压 值: 200V AC/minute
适用基板厚度: 1.6mm

16	12.00	15.00
15	11.20	14.20
14	10.40	13.40
13	9.60	12.60
12	8.80	11.80
11	8.00	11.00
10	7.20	10.20
9	6.40	9.40
8	5.60	8.60
7	4.80	7.80
6	4.00	7.00
5	3.20	6.20
4	2.40	5.40
3	1.60	4.60
2	0.80	3.80
Pin	DIM.A	DIM.B

4	Cap	1 PCS	材质: LCP (UL94V-0), 颜色: 本色或黑色
3	FITTING NAIL	2 PCS	材质: 磷青铜, 电镀: 镀亮锡
2	PIN	n PCS	材质: 磷青铜, 电镀: 镀亮锡
1	Housing	1 PCS	材质: LCP (UL94V-0), 颜色: 本色
NO.	NAME	Q'TY	DESCRIPTION

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	0800WVS-XXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	0800WVS-XXP			X.x ±0.20		
			3RD ANGLE PROJ		HanElectricity Co.,LTD		X.xx ±0.15		ANGULAR ±3°
						FILE.NO.			