





1. 极数 Number of poles: 2-16
2. 工作温度 Working Temperature: -40°C $- +85^{\circ}\text{C}$
3. 额定电压 Voltage rating : 125V AC
4. 额定电流 Rated current : 1A
4. 接触电阻 Contact resistance: $\leq 30\text{m}\Omega$
5. 绝缘电阻 Insulation resistance: $\geq 100\text{M}\Omega$
6. 耐压 Withstand voltage : 250V AC
7. 端子 Terminal : 铜合金 Copper Alloy
外壳 Housing : LCP

Part No	PIN	A	B	C
BX-MX1.25-2PLT-XW	2	1.25	4.30	7.05
BX-MX1.25-3PLT-XW	3	2.50	5.55	8.30
BX-MX1.25-4PLT-XW	4	3.75	6.80	9.55
BX-MX1.25-5PLT-XW	5	5.00	8.05	10.80
BX-MX1.25-6PLT-XW	6	6.25	9.30	12.05
BX-MX1.25-7PLT-XW	7	7.50	10.55	13.30
BX-MX1.25-8PLT-XW	8	8.75	11.80	14.55
BX-MX1.25-9PLT-XW	9	10.00	13.05	15.80
BX-MX1.25-10PLT-XW	10	11.25	14.30	17.05
BX-MX1.25-11PLT-XW	11	12.50	15.55	18.30
BX-MX1.25-12PLT-XW	12	13.75	16.80	19.55
BX-MX1.25-13PLT-XW	13	15.00	18.05	21.80
BX-MX1.25-14PLT-XW	14	16.25	19.30	22.05
BX-MX1.25-15PLT-XW	15	17.50	20.55	23.30
BX-MX1.25-16PLT-XW	16	18.75	21.80	24.55



PCB.焊接图
PCB.WELDING DRAWING

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX—MX1.25—NPLT—XW		版本 REV.	A	
			≥0~2 ± 0.20	±0.5°		审核 CHECK	EVA	品名 TITLE		WAFER 1.25 立贴	页次 SHEET			1/1
			≥2~5 ± 0.30											
			≥5 ± 0.50											
		单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)								