




1. 特性:

额定电压 : 500V AC MIN

小针额定电流 :5A

大针额定电流 :10A, 20A, 30A, 40A

接 触 阻 抗 :30mΩ MAX.

绝 缘 阻 抗 :3000MΩ MIN. at 500V DC

耐电压值 :1000V AC RMS for 1Minute

温度范围：-55℃-+105℃

盐雾时间：48H

2. 材料:

胶 芯 : PBT, rated UL94V-0

接触点: 铜合金, 镀金1u"-30u"

铁壳：SPCC，前壳镀镍后壳镀锡

额定电流	ΦA	ΦB	适用线径
10A	Φ2.60	Φ1.80	14~16AWG
20A	Φ3.60	Φ2.80	10~12AWG
30A	Φ4.50	Φ3.50	8~10AWG
40A	Φ5.40	Φ4.60	6~8AWG

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: DW-25W3M 公头 焊线式 长针 全金 光孔					
DRAWN: LYF	DATE: 2024-01-13	PART. NO.		D-DW0025PM-A000			
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-DW-00041	REV.	A	QT00	