

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE
			A	H
			φ2.4	3.5
			φ2.35	3.8
			φ2.35	4.0
			φ2.3	4.5
			φ2.3	4.8
			φ2.3	5.0
			φ2.2	5.5
			φ2.2	6.0
			φ2.15	6.5
			φ2.2	7.0
			φ2.1	8.0
			φ2.05	9.0

A

B

C

D

E

F

G

A

B




C

D

E



F

G




技术参数:

- 1.使用温度: -25~+85℃
- 2.额定负荷: DC 12V 50mA
- 3.接触电阻: ≤50mΩ
- 4.绝缘电阻: ≥100MΩ
- 5.耐 压: AC250V(50Hz)/min
- 6.动 作 力: 260±50g
- 7.使用寿命: 50,000次



PCB线路板安装图(±0.1)




电路图

3	盖板	冷轧钢	Cu/Sn	
2	弹片	不锈钢	— —	
1	基座	PPA	黑色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	轻触开关
料 号 PART NO	HC-QC454535-T-R

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1			
X. ±0.20	X'. ±1°	单 位 UNIT	MM	制 图 DRAW	AhYe	
.X ±0.15	.X' ±0.5°	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
.XX ±0.05	.XX' ±0.1°	版 本 REV	A	批 准 APPROVE	赵亮亮	