








Specification:

- Voltage rating: 250V AC/DC
- Current rating: 5A AC/DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
- Insulation resistance: $\geq 1000\text{M}\Omega$
- Contact resistance: $\leq 10\text{m}\Omega$
- After environmental testing: $\leq 20\text{m}\Omega$
- Material(Pin): Brass
- Mates with AXDZ housing :MX30H-2xXP



Pin	DIM		
	A	B	C
2*1P	---	6.65	2.0
2*2P	3.00	9.65	2.0
2*3P	6.00	12.65	2.0
2*4P	9.00	15.65	6.70
2*5P	12.00	18.65	9.70
2*6P	15.00	21.65	12.70
2*7P	18.00	24.65	15.70
2*8P	21.00	27.65	18.70
2*9P	24.00	30.65	21.70
2*10P	27.00	33.65	24.70
2*11P	30.00	36.65	27.70
2*12P	33.00	39.65	30.70



Type1~Type2
P.C.B Layout

		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	3025WV-2xXXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	3025WV-2xXXP			X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx ±0.15	
							ANGULAR	±3°	
							FILE.NO.		