



说明:

1. 特性:

额定电压 :500V AC MIN

小针额定电流 :5A

大针额定电流 :10A, 20A, 30A, 40A

接触阻抗 :30mΩ MAX.

绝缘阻抗 :3000MΩ MIN. at 500V DC

耐电压值 :1000V AC RMS for 1Minute

温度范围 : -55℃~+105℃

盐雾时间 : 48H

2. 材料:

胶芯 : PBT, rated UL94V-0

接触点: 铜合金, 镀金1u"-30u"

铁壳 : SPCC, 前壳镀镍后壳镀锡

额定电流	Ø A	Ø B	适用线径
10A	Ø 2.60	Ø 1.80	14~16AWG
20A	Ø 3.60	Ø 2.80	10~12AWG
30A	Ø 4.50	Ø 3.50	8~10AWG
40A	Ø 5.40	Ø 4.60	6~8AWG

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD					
CHECKED:	DATE:	TITLE: DW-24W7F 母头 焊线式 长针 全金 光孔					
DRAWN: LYF	DATE: 2024-04-07	PART. NO.		D-DW0024PF-A000			
		UNIT	mm	SCALE	free	☉	☐
		FILE NO.		Ckmtw-DW-00015		REV.	A QT00