






REV.	DESCRIPTION	ECN NO.	NAME	DATE



序号	品名	材质
1	XH2.5 胶芯	PA66 UL94V-2 Red
2	XH2.5 弯针 端子	Copper Alloy/ Tin Plating

Technical Index:

1. Temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.

2. Rated voltage: 250V

 $DC/AC(rms).$


3. Rated current: 3.0A.

4.Contact resistance: $\leq 20\text{m}\Omega$.

5. Withstanding voltage: 1000V

AC/minute.

6. Insulation resistance: $\geq 1000\text{M}\Omega$.



适用线路板(PCB LAYOUT)

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. TOL. x. ±0.50 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: x° ±5° x.x' ±3° x.xx" ±1°		TITLE: XH2.5 弯针					
		DWG. NO.: AF-XH2.54-NPWZ-R2		CHECKED: MAX			
		PART NO.: AF-XH2.54-NPWZ-R2		DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL