REV.	DESCRIPTION	ECN NO.	NAME	DATE



Part No	Pin	A	B	C	D
AF-XH2.54-2PJK-W1	2	2.50	5.70	3.70	3.70
AF-XH2.54-3PJK-W1	3	5.00	8.20	6.20	6.20
AF-XH2.54-4PJK-W1	4	7.50	10.70	8.70	8.70
AF-XH2.54-5PJK-W1	5	10.00	13.20	11.20	11.20
AF-XH2.54-6PJK-W1	6	12.50	15.70	13.70	13.70
AF-XH2.54-7PJK-W1	7	15.00	18.20	16.20	16.20
AF-XH2.54-8PJK-W1	8	17.50	20.70	18.70	18.70
AF-XH2.54-9PJK-W1	9	20.00	23.20	21.20	21.20
AF-XH2.54-10PJK-W1	10	22.50	25.70	23.70	23.70
AF-XH2.54-11PJK-W1	11	25.50	28.20	26.20	26.20
AF-XH2.54-12PJK-W1	12	27.50	30.70	28.70	28.70
AF-XH2.54-13PJK-W1	13	30.00	33.20	31.20	31.20
AF-XH2.54-14PJK-W1	14	32.50	35.70	33.70	33.70
AF-XH2.54-15PJK-W1	15	35.50	28.20	36.20	36.20
AF-XH2.54-16PJK-W1	16	37.50	40.70	38.70	38.70

技术要求Specification:

1、材质Material: PA66 UL94V-0;
2、额定电流 Current rating:3.0A AC,DC
3、额定电压 Voltage rating:250V AC,DC
4、温度范围 Temperature range:-25℃to+85℃
5、接触电阻 Contact resistance:≤20mΩ
6、绝缘电阻Insulation resistance:≥1000MΩ
7、耐压Withstand voltage:1000V AC/minute
8、塑件表面平整光洁，无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象.
Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.



GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		BXCONN®
DIM.	TOL.	TITLE: XH2.5MM HOUSING		
.x	±0.30			
.xx	±0.20			
.xxx	±0.10			
GENERAL ANGLE:				
x.°	±1°	DWG. NO.: AF-XH2.54-NPJK-W1	CHECKED: MAX	
		PART NO.: AF-XH2.54-NPJK-W1	DRAWN: ELLA	
		UNIT: mm / SCALE: none / SHEET: 1of 1 / DWG. SIZE: A4 / LAYER: bxconn	APPROVED: WILL	