






技术指标:

1. 额定电流: 0.5A
2. 温度范围: -40~85℃
3. 额定电压: 50V, AC/DC (等效)
4. 接触电阻: $\leq 0.03\Omega$
5. 绝缘电阻: $\geq 500M\Omega$



Part No	Pin	A	B	C
ZX-0.5FPC-2H-QF4P	4	1.50	2.60	6.40
ZX-0.5FPC-2H-QF5P	5	2.00	3.10	6.90
ZX-0.5FPC-2H-QF6P	6	2.50	3.60	7.40
ZX-0.5FPC-2H-QF7P	7	3.00	4.10	7.90
ZX-0.5FPC-2H-QF8P	8	3.50	4.60	8.40
ZX-0.5FPC-2H-QF9P	9	4.00	5.10	8.90
ZX-0.5FPC-2H-QF10P	10	4.50	5.60	9.40
ZX-0.5FPC-2H-QF11P	11	5.00	6.10	9.90
ZX-0.5FPC-2H-QF12P	12	5.50	6.60	10.40
ZX-0.5FPC-2H-QF13P	13	6.00	7.10	10.90
ZX-0.5FPC-2H-QF14P	14	6.50	7.60	11.40
ZX-0.5FPC-2H-QF15P	15	7.00	8.10	11.90
.....		...		
ZX-0.5FPC-2H-QF61P	60	(61-1)*0.5	(61+1)*0.5+0.1	(61+7)*0.5+0.9

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-0.5FPC-2H-QFNP	版本 REV.	A		
						X.:±0.15	±1°		审核 CHECK	LEO							
											X.X:±0.10					核准 APPROVAL	JOHN
1	端子	磷青铜/表面镀锡										品名 TITLE	0.5-B翻盖(H:2.0)	页次 SHEET	1/1		
2	焊片	黄铜/表面镀锡				X.X:±0.10					客户料号 CUTM.NO.						
3	基座	LCP UL94V-0 本色				X.XX:±0.05											
4	锁条	LCP UL94V-0 黑色															