





标记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修改 REVISE	日期 DATE	核准 APPROVE

编号	尺寸 (mm)	
	A	B
2A	2.50	7.50
3A	5.00	10.00
4A	7.50	12.50
5A	10.00	15.00
6A	12.50	17.50
7A	15.00	20.00
8A	17.50	22.50
9A	20.00	25.00
10A	22.50	27.50
11A	25.00	30.00
12A	27.50	32.50



SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: Wafer Nylon66
PIN Brass Tin-plated



2	插针	铜	镀锡	
1	基座	PA66	米色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品名 TITLE	针座
			料号 PART NO	5264-8A-TM

GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1		
X±0.25	X*±2'	单位 UNIT	MM	制图 DRAW	AhYe
.X±0.20	.X*±1'	张数 PART NO	1 OF 1	审核 CHECKED	夏操云
.XX±0.15	.XX*±0.5'	版本 REV	A	批准 APPROVE	赵亮亮
.XXX±0.10	.XXX*±0.5'				