







修 订	标 记	修 改 描 要	签 名	日 期
REV A0		NEW DRG		2016-03-12



RECOMMEND P.C.B LAYOUT
TOP VIEW TOLERANCE:±0.05



NOTES:

* MATERIAL:

- 1.HOUSING:LCP+30%G/F,UL94 V-0,Color:Black;
- 2.CONTACT: Brass, T=0.40mm;
- 3.Shell: STAINLESS STEEL, T=0.20mm.



* FINISH:

1.CONTACT:

GOLD PLATED ALL OVER;
NICKEL UNDER PLATED ALL OVER.

2.Shell:

Ni UNDER PLATED OVER ALL;
Matte Tin Plated Over All.



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: 唐虞1.5卧贴针座	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC1507WR-S-7P
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	SCALE
			UNIT
			CODE NUMBER
		2016-03-12	1:1
			mm
			A001