



Recommended FPC Dimension

Note:

1. Material:
 - 1.1: Housing: NYLON46 UL94-V0 Color:NATURE.
 - 1.2: Actuator: PPS UL94-V0 Color:NATURE.
 - 1.3: Contact: Phosphor Bronze.
 - 1.4: LEG: Brass.
2. Plating:
 - 2.1: Contact: Gold Flash or Tin.
 - 2.2: LEG: Matte Tin Plating Over Nickel.
3. Rating:
 - 3.1: Operating Voltage: 50V AC/DC.
 - 3.2: Current Rating: 0.4A AC/DC.
 - 3.3: Operating Temperature: -25°C~+85°C.

PORT NO	Dimension				
	A	B	C	D	E
30P	35.20	34.90	29.00	36.60	31.20
26P	31.20	30.90	25.00	32.60	27.20
24P	29.20	28.90	23.00	30.60	25.20
16P	21.20	20.90	15.00	22.60	17.20



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: FPC 1.0间距3.6厚5.75高立贴抽展式			
X.X	±0.30	X.X*	±3°	PART NO: 产品编号: 1.0K-3.6CT-nPB			
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm