



REV.	DESCRIPTION	DATE
A	首次发行	2025-12-2



技术要求:

- 1) 标准阻抗: 50 OHM;
- 2) 频率范围: 0~6 GHz;
- 3) 电压驻波比: 1.5 MAX;
- 4) 工作电压: 335~500 Volts;
- 5) 电介质耐电压: 500~1500Vrms;
- 6) 绝缘阻抗: 5000 mehoHms min



序号	名称	本厂料号	材质	数量	表面处理
4	绝缘体	04-001201-AX	铁弗龙	1	素材
3	绝缘体	04-001200-AX	铁弗龙	1	素材
2	中心针	03-001301-AX	黄铜	1	镀金
1	本体	02-001311-AZ	黄铜	1	镀金

			
东莞市众驰电子有限公司			
Dongguan Zhongchi Electronic Co., Ltd			
Tel:0769-81238620			
Fax:0769-81238620			
PART NAME: SMA JACK PCB			
PART NO.: ZC8.26565L4.2KE		DATE: 2025-12-2	
APPROVED BY	CHECKED BY	DESIGNED BY	
		HYH	
UNITS: mm		Tolerance	
SCALE: 1/1		x ±0.30	
REVISION: 1		x.x ±0.20	
		x.x ±0.10	
		ANGULAR @5°	