



REV.	DESCRIPTION	DATE
A	首次发行	2025-3-13



技术要求:

- 1) 标准阻抗: 50 OHM;
- 2) 频率范围: 0~6 GHz;
- 3) 电压驻波比: 1.5 MAX;
- 4) 工作电压: 335~500 Volts;
- 5) 电介质耐电压: 500~1500Vrms;
- 6) 绝缘阻抗: 5000 mehoams min
- 7) 内导体: $\leq 30\text{m}\Omega$ 外导体: $\leq 30\text{m}\Omega$
- 8) 材质: 中心导体及外导体: 黄铜合金 (C3604), 镀金, 胶芯: PTFE
- 9) 盐雾: 48H
- 10) 工作温度: $-65^{\circ}\text{C}\sim+165^{\circ}\text{C}$, 储存温度: $-30^{\circ}\text{C}\sim+60^{\circ}\text{C}$

				
东莞市众驰电子科技有限公司				
Dongguan Zhongchi Electronic Technology Co., Ltd Tel 0769-81238620 Fax 0769-81238620				
PART NAME: SMA母头母针夹板连接器		DATE: 2025-3-13		
PART NO.: ZC8.13565L1.2KE				
APPROVED BY	CHECKED BY	DESIGNED BY		Tolerance
		HYH	UNITS: mm SCALE: 1/1	X X ± 0.20 X.XX ± 0.15 X° $\pm 3^{\circ}$
			REVISION: B	