







修 订	标 记	修 改 描 要	签 名	日 期
REV	AO	REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12




SECTION A-A



- SPECIFICATION:
1. RATING: DC 20V 7A
 2. CONTACT RESISTANCE: 30mΩ MAX.
 3. INSULATION RESISTANCE: 100 MΩ MIN.
 4. WITHSTAND VOLTAGE: 500 VAC
 5. INSERTION FORCE: 3N~30N
 6. EXTRACTION FORCE: 3N~30N
 7. DURABILITY: 5,000 CYCLES



MATING PLUG
DP400170-0038-6H



RECOMMENDED PCB LAYOUT(T=1.00)
TOP VIEW TOLERANCE:±0.05

SCHEMATIC	
	1# (+)
	2#/3#4#/5# (-)

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
C	CENTER PIN	BRASS	GOLD FLASH/Ni 40u"	1
B	SHELL	COPPER ALLOY	Ni 40u"	1
A	HOUSING	HIGH TEMP.THERMOPLASTIC	BLACK	1

HDC 深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: DC Power Jack 4017 大电流8A, 卧式, 产品名称: 高可靠, 四脚插板CL=2.88	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: DC400170-1094-2H
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12 1:1 mm A001