









SPECIFICATION

1. Rating : DC 12V, 3.0A;
2. Contact resistance: 30mΩ MAX;
3. Insulation resistance: 100MΩ MIN.;
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3—20N
6. life test: 5,000 cycles.

RECOMMENDED PCB LAYOUT
TOP VIEW TOLERANCE:±0.05



SECTION A-A



MATING PLUG

P/N.: DP350135-0120-6H

D	PIN	1	HB159	Gold flash/Ni
C	CURVE PIECE	1	SUS 304	Ni
B	SPRING	1	C5191	Sn/Ni
A	HOUSING	1	PA46 BLACK	_____
NO.	DESCRIPTION	QTY	MATERIAL	PLATING



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co., LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: DC Power Jack 35135 大电流5A, 四 产品名称: 式, 高可靠, 两脚插板CI=2.45			
X.X ±0.30	X.X* ±3°	APPD: 核准:		PART NO: DC350135-0831-2H 产品编号:			
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业		DATE	SCALE	UNIT	CODE NUMBE
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰		2016-03-12	1:1	mm	A001