

A

B


C

D



E

F

修订	标记	修改摘要	签名	日期
REV	NO	NEW DWG		
				2016-03-12







Ø6.00
PICK UP



SECTION A-A


SPECIFICATION:

1. RATING: DC 30V 12A
2. CONTACT RESISTANCE:
30mΩ MAX(INITIAL).
50mΩ MAX(FINAL).
3. INSULATION RESISTANCE: 100 MΩ MIN.
4. WITHSTAND VOLTAGE: 500 VAC
5. INSERTION FORCE: 30N MAX.
6. EXTRACTION FORCE: 3N MIN.
7. DURABILITY: 5,000 CYCLES

MATING PLUG
DP550250-0188 -6H

RECOMMENDED PCB LAYOUT
TOP VIEW TOLERANCE:±0.05

PRODUCT EDGE



D	GROUND	SUS 304		1
C	SHELL	C5210	Ni 40u" MIN.	1
B	CENTER PIN	BRASS	GOLD FLASH /Ni 40u" MIN.	1
A	HOUSING	PA10T	BLACK	1
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: DC Power Jack 5525 大电流12A, 卧 产品名称: 式, 高可靠, 四脚插板CL=5.10	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: DC550250-0991-2H
X.XX ±0.20	X.XX* ±2°	CHECK: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 黄艳兰 绘图:	2016-03-12 1:1 mm A001