







修 订	标 记	修 改 描 述	签 名	日 期
REV AO		NEW DWG		2016-03-12



SECTION A-A




RECOMMENDED PCB LAYOUT
TOP VIEW TOLERANCE: ± 0.05



SCHEMATIC
1#(+)
2#/3#4#(-)

SPECIFICATION:

- RATING: DC 20V 20A
- CONTACT RESISTANCE:
30m Ω MAX.(INITIAL)
50m Ω MAX.(FINAL)
- INSULATION RESISTANCE: 100 M Ω MIN.
- WITHSTAND VOLTAGE: 500 VAC
- INSERTION FORCE: 3N~30N
- EXTRACTION FORCE: 3N~30N
- DURABILITY: 5,000 CYCLES



MATING PLUG
DP550250-0188-6H

E	MYLAR			1
D	GROUND	SUS 304		1
C	SHELL	COPPER ALLOY	Ni 40u"MIN.	1
B	CENTER PIN	BRASS	GOLD FLASH/Ni 40u" MIN.	1
A	HOUSING	HIGH TEMP.THERMOPLASTIC	BLACK	1
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			TITLE: DC Power Jack 5525 大电流20A, 直 产品名称: 立式, 高可靠 H=14.0			
X.X	± 0.30	X.X*	$\pm 3^{\circ}$	APPD: 核准:	PART NO: 产品编号: DC550250-1077-2H	
X.XX	± 0.20	X.XX*	$\pm 2^{\circ}$	CHECK: 校对: 王建业	DATE	SCALE
X.XXX	± 0.10	X.XXX*	$\pm 1^{\circ}$	DRAW: 绘图: 黄艳兰	2016-03-12	1:1
				UNIT	CODE NUMBER	
				mm	A001	