







A B C D E F

修订	标记	修改摘要	签名	日期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
AO		NEW DWG		2016-03-12



RECOMMENDED PCBA LAYOUT
(TOLERANCE+/-0.05)



NOTES:

1. ELECTRONIC:

CONTACT CURRENT RATING: 1.5A

CONTACT RESISTANCE: 30mohm Max

INSULATION RESISTANCE: 100 Megohms Min

WITHSTAND VOLTAGE: AC100V, 1Min.

2. MECHANICAL:

MATING FORCE: 3.57KG Max

UNMATED FORCE: 0.8KG Min

DURABILITY: 1500 CYCLES

3. ENVIRONMENT CHARACTERISTICS:

OPERATING TEMPERATURE: -40° C TO +85° C

3	SHELL	1	COPPER ALLOY/SUS/SPCC	NI PLATED
2	CONTACT	9	COPPER ALLOY	AU /TIN PLATED
1	HOUSING	1	THERMOPLASTIC(LCP)	(UL 94V-0)
No.	PART NAME	QTY	MATERIAL	REMARK

PIN NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND
5	StdA_SSRX-
6	StdA_SSRX+
7	GND_DRAIN
8	StdA_SSTX-
9	StdA_SSTX+
Shell	Shield




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话：0755-27111216 传真：0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE: USB 3.2 Gen2 AF SMT 沉板H=2.1MM
产品名称: 外壳 无卷边 不锈钢壳 LCP橙色

PART NO: USB3.0-GD-103PWB
产品编号:

APPD: 核准: 王建业

DATE SCALE UNIT CODE NUMBER

CHECK: 校对: 黄艳兰

2016-03-12 1:1 mm A001

DRAW: 绘图:

A B C D E F