








修 订 REV NO	标 记 MARK	修 改 描 要 REVISION DESCRIPTION	签 名 SIGNATURE	日 期 DATE
		NEW DWG		2016-03-12



SECTION A-A



RECOMMENDED PCB LAYOUT
TOP VIEW TOLERANCE: ± 0.05



MATING PLUG
DP550250-0188-6H

SPECIFICATION:

1. RATING: DC 20V 20A
2. CONTACT RESISTANCE:
30m Ω MAX.(INITIAL)
50m Ω MAX.(FINAL)
3. INSULATION RESISTANCE: 100 M Ω MIN.
4. WITHSTAND VOLTAGE: 500 VAC
5. INSERTION FORCE: 3N~30N
6. EXTRACTION FORCE: 3N~30N
7. DURABILITY: 5,000 CYCLES

SCHEMATIC	
	1#(+)
	2#/3#4#(-)

E	MYLAR			1
D	GROUND	SUS 304		1
C	SHELL	COPPER ALLOY	Ni 40u" MIN.	1
B	CENTER PIN	BRASS	GOLD FLASH/Ni 40u" MIN.	1
A	HOUSING	HIGH TEMP.THERMOPLASTIC	BLACK	1
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co., LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE: DC Power Jack 5525 大电流20A, 直
产品名称: 立式, 高可靠 H=12.6

X.X	± 0.30	X.X*	$\pm 3^{\circ}$	APPD: 核准:	PART NO: 产品编号:	DC550250-1075-2H			
X.XX	± 0.20	X.XX*	$\pm 2^{\circ}$	CHECK: 校对:	DATE	SCALE	UNIT	CODE NUMBER	
X.XXX	± 0.10	X.XXX*	$\pm 1^{\circ}$	DRAW: 绘图:	黄艳兰	2016-03-12	1:1	mm	A001