











RECOMMENDED PCB LAYOUT
TOP VIEW TOLERANCE: ± 0.05



SPECIFICATION:

1. RATING: DC 20V 20A
2. CONTACT RESISTANCE:
30m Ω MAX.(INITIAL)
50m Ω MAX.(FINAL)
3. INSULATION RESISTANCE: 100 M Ω MIN.
4. WITHSTAND VOLTAGE: 500 VAC
5. INSERTION FORCE: 3N~30N
6. EXTRACTION FORCE: 3N~30N
7. DURABILITY: 5,000 CYCLES



MATING PLUG
DP550250-0188-6H

E	MYLAR			1			
D	GROUND	SUS 304		1			
C	SHELL	COPPER ALLOY	Ni 40u"MIN.	1			
B	CENTER PIN	BRASS	GOLD FLASH/Ni 40u" MIN.	1			
A	HOUSING	HIGH TEMP.THERMOPLASTIC	BLACK	1			
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY			
 深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话：0755-27111216 传真：0755-29940187							
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 	TITLE: DC Power Jack 5525 大电流20A, 直 产品名称: 立式, 高可靠 H=17.5				
X.X	±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: DC550250-1080-2H			
X.XX	±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001