







3D VIEW



SPECIFICATION:

1. RATING: DC 20V 5A
2. CONTACT RESISTANCE: 30mΩ MAX.
3. INSULATION RESISTANCE: 100 MΩ MIN.
4. WITHSTAND VOLTAGE: 500 VAC
5. INSERTION FORCE: 2.0Kgf MAX.(INITIAL)
2.0Kgf MAX.(FINAL)
6. EXTRACTION FORCE: 1Kgf~3.0Kgf(INITIAL)
0.7Kgf~3.0Kgf(FINAL)
7. DURABILITY: 10,000 CYCLES

SCHEMATIC



MATING PLUG

P/N.:DP400170-0038-60000H

D	STOPPER	SUS 304		1
C	CENTER PIN	C3602	Sn100u"/Ni 50u"	1
B	SHELL	C5210	Ni 50u"	1
A	HOUSING	PA10T	BLACK	1
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: DC Power Jack 4017 大电流8A, 焊线 产品名称: 式, 高可靠, 焊线式	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: DC400170-0119-6H
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12 1:1 mm A001