





ROHS



PCB LAYOUT General±0.05mm.

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Voltage Rating: 250V
Current Rating: 1AMP
Temperature Range: -40°Cto+105°C
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 500V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING		TITLE 排针 PIN距1.27 塑高1.0 双排5PIN直插		REV. A		
CHECKED						
APPROVED						
TOLERANCES ARE		PART NO. LAIL-PZ1. 27-5PX2-L	UNITS mm	Projection		
30-150	±0.35					ANGLE ±3°
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
DWG. NO.						