




ROHS



PCB LAYOUT General±0.05mm.

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: 250V

Current Rating: 1AMP

Temperature Range: -40°Cto+105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 500V


Material:

Insulator: Polyester (UL94V-0)

Standard: PA6T

Contact: Brass

Plating: Au over Ni



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECKED					
APPROVED					
TOLERANCES ARE		TITLE	排针 PIN距1.27 塑高1.0 双排4PIN立贴	REV.	A
30-150	±0.35	PART NO.	LAIL-PZ1.27-4PX2-T	UNITS	mm
10-30	±0.2				
5-10	±0.15	DWG. NO.			Projection
0-5	±0.1				