





Poles	PART NO.	Dimension mm	
		A	B
2*1	W-5557M02P-B000	/	5.60
2*2	W-5557M04P-B000	4.20	9.80
2*3	W-5557M06P-B000	8.40	14.00
2*4	W-5557M08P-B000	12.60	18.20
2*5	W-5557M10P-B000	16.80	22.40
2*6	W-5557M12P-B000	21.00	26.60
2*7	W-5557M14P-B000	25.20	30.80
2*8	W-5557M16P-B000	29.40	35.00
2*9	W-5557M18P-B000	33.60	39.20
2*10	W-5557M20P-B000	37.80	43.40
2*11	W-5557M22P-B000	42.00	47.60
2*12	W-5557M24P-B000	46.20	51.80

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

SPECIFICATION

Voltage rating:AC,DC 300V

Current rating:AC,DC,7A

Withstand voltage:1500V AC min.

Insulation resistance:1000M Ω min.

Temperature range:-25℃~+85℃

Applicable PC board thickness:0.031"~0.063"
(0.8~1.6mm)

Contact resistance:Initial value 10m Ω max.


After environmental testing 20m Ω max.

Material:PA66 UL94V-0(2)

Contact:Brass

Finish:Tin-plated

Color:White



APPROVED:	DATE:	 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 5557SMT-2*XP 立贴 方针 白色			
DRAWN: LYF	DATE: 2024-04-18	PART. NO.	W-5557MXXP-B000		
		UNIT	mm	SCALE	free
		FILE NO.	CKMTW-5557-0035	REV.	A ZW00