




ROHS



PCB LAYOUT

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: AC 250V

Current Rating: 3AMP

Temperature Range: -40°C~+105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 1000V


Material:

Insulator: Polyester (UL94V-0)

Standard: PA9T

Contact: Brass

Plating: Au over Ni



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED					
APPROVED					
TOLERANCES ARE		TITLE	排母 PIN距2.54 塑高8.5 单排4PIN弯针	REV.	A
30-150	±0.35	PART NO.	LAIL-PM2.54-4P-W	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1	DWG. NO.		Projection	
ANGLE		±3°			