




ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Voltage Rating: 250V
Current Rating: 3AMP
Temperature Range: -40℃to+105℃
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 1000V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni



PCB LAYOUT General±0.05mm.

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司					
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD					
CHECKED							
APPROVED							
TOLERANCES ARE		TITLE		排针 PIN距2.54 塑高2.5 单排40PIN直插		REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PZ2.54-40P-L		UNITS	mm
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
		±3°	DWG. NO.			Projection	