




Recommand PCB Layout

Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -40° C~+105° C
- Insulation resistance:100MΩ Min
- Contact resistance: 20mΩ Max

Reference Informations:

*Material:

PIN:Brass

Plating: Gold-flash or Tin-plated

Wafer: PBT,UL94V-0

Color: Black,

Ordering Information & Dimensions

Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
2*3P	5.08	10.12	8.02	2*21P	50.80	55.84	53.74
2*4P	7.62	12.66	10.56	2*22P	53.34	58.38	56.28
2*5P	10.16	15.20	13.10	2*23P	55.88	60.92	58.82
2*6P	12.70	17.74	15.64	2*24P	58.42	63.46	61.36
2*7P	15.24	20.28	18.18	2*25P	60.96	66.00	63.90
2*8P	17.78	22.82	20.72	2*26P	63.50	68.54	66.44
2*9P	20.32	25.36	23.26	2*27P	66.04	71.08	68.98
2*10P	22.86	27.90	25.80	2*28P	68.58	73.62	71.52
2*11P	25.40	30.44	28.34	2*29P	71.12	76.16	74.06
2*12P	27.94	32.98	30.88	2*30P	73.66	78.70	76.60
2*13P	30.48	35.52	33.42	2*31P	76.20	81.24	79.14
2*14P	32.02	38.06	35.96	2*32P	78.74	83.78	81.68
2*15P	35.56	40.60	38.50				
2*16P	38.10	43.14	41.05				
2*17P	40.64	45.68	43.58				
2*18P	43.18	48.22	46.12				
2*19P	45.72	50.76	48.66				
2*20P	48.26	53.30	51.20				

DC

2.50mm

2.90mm

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD					
CHECKED:	DATE:	TITLE: 2547S-2*12P 带扣 DC=2.9mm 黑色					
DRAWN: LYF	DATE: 2019-05-07	PART. NO.		W-2547S24P-B000			
		UNIT	mm	SCALE	free	⊕	⊖
		FILE NO.	Ckmtw-2547-00003			REV.	A LYDZ

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05