




ROHS



PCB LAYOUT General±0.05mm.

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: 250V

Current Rating: 3AMP

Temperature Range: -40°Cto+105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage : AC 1000V


Material:

Insulator: Polyester (UL94V-0)

Standard: PA6T

Contact: Brass

Plating: Au over Ni



CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
CHECKED							
APPROVED							
TOLERANCES ARE			TITLE		排针 PIN距2.54 塑高2.5 双排5PIN弯针	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PZ2.54-5PX2-W	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG. NO.			Projection	