


HSF





RoHS



Specifications

- 1.Contact Resistance: <10mΩ
2.Insulation Resistance: >100MΩ



Ordering Code:

OBD-FMB - 16 - G0 - X - X - X - V2
① ② ③ ④ ⑤ ⑥ ⑦

① OBD Framed Full

② Contact Number: 16P

③ Contact Plating

G0: Gold flash

G1: 3u" Gold

G2: 5u" Gold

G3: 10u" Gold

G4: 15u" Gold

G5: 30u" Gold

SN: Tin

④ Color Insulator

W: White B: Black

⑤ Insulator Material

A: PBT B: PA6T

C: LCP D: PA46

E: PA9T

⑥ Packing

A: Tray B: Bag

C: Reel

⑦ Series No: V2

Unless Otherwise specified tolerance
X.±0.35 X.XX:±0.20
X.X:±0.25 X.XXX:±0.15

SCALE:

As Shown

UNIT:

mm

DRAW

ZLA

DATE

10/05/2023

CHECK

BobYang

DATE

10/05/2023

VER./版本号



3rd ANGLE PROJECTION



ANTENK ELECTRONICS CO.,LTD
Http://www.antenk.com
E-mail:sales@antenk.com

TITLE:

OBD Male 16P Framed Connector

DRAWING NO: OBD-FMB-16G0XXXV2

PRODUCT NO: OBD-FMB-16G0XXXV2

Increase Packing: "Reel"

Redraw Based on 3D

DESCRIPTION/修订内容

10/08/2025

10/17/2023

DATE/日期 M/D/Y



MK/标记