





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Voltage Rating: AC 250V
Current Ratin : 1AMP
Temperature Range: -40°C~+105°C
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 500V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA9T
Contact: C5159
Plating: Au over Ni



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECKED							
APPROVED							
TOLERANCES ARE			TITLE		排母 PIN距1.27 塑高4.3 双排5PIN立贴	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PM1.27-5PX2-T	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG. NO.	Projection			