





ROHS

| REV. | ECN NO. | DESCRIPTION | DRAW | DATE |
|------|---------|-------------|------|------|
|      |         |             |      |      |

SPECIFICATION:  
Voltage Rating: 250V  
Current Rating: 3AMP  
Temperature Range: -40℃to+105℃  
Contact Resistance: 20mΩ Max  
Insulation Resistance: 1000MΩ Min  
Withstanding Voltage: AC 1000V  
Material:  
Insulator: Polyester (UL94V-0)  
Standard: PA6T  
Contact: Brass  
Plating: Au over Ni



PCB LAYOUT General±0.05mm.

| CUSTOMER DRAWING |       |       | LAILIAN 深圳市莱联电子有限公司                  |                            |            |    |
|------------------|-------|-------|--------------------------------------|----------------------------|------------|----|
| DRAWING          |       |       | SHENZHEN LAILIAN ELECTRONICS CO.,LTD |                            |            |    |
| CHECKED          |       |       |                                      |                            |            |    |
| APPROVED         |       |       |                                      |                            |            |    |
| TOLERANCES ARE   |       |       | TITLE                                | 排针 PIN距2.54 塑高2.5 单排6PIN直插 | REV.       | A  |
| 30-150           | ±0.35 | ANGLE | PART NO.                             | LAIL-PZ2.54-6P-L           | UNITS      | mm |
| 10-30            | ±0.2  |       | DWG. NO.                             |                            | Projection |    |
| 5-10             | ±0.15 |       |                                      |                            |            |    |
| 0-5              | ±0.1  |       |                                      |                            |            |    |