


ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Voltage Rating: 250V
Current Rating: 2AMP
Temperature Range: -40℃to+105℃
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 500V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni



PCB LAYOUT General±0.05mm.

CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING			TITLE		排针 PIN距2.0 塑高2.0 单排3PIN直插	REV.	A
CHECKED							
APPROVED							
TOLERANCES ARE			PART NO.	LAIL-PZ2. 0-3P-L	UNITS	mm	
30-150	±0.35	ANGLE					
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
		±3°	DWG. NO.		Projection		