




ROHS



PCB LAYOUT

| REV. | ECN NO. | DESCRIPTION | DRAW | DATE |
|------|---------|-------------|------|------|
|      |         |             |      |      |

SPECIFICATION:

Current Rating: 3AMP

Temperature Range: -40°C~+105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 1000V


Material:

Insulator: Polyester (UL94V-0)

Standard: PA9T

Contact: Brass

Plating: Au over Ni



|                  |       |       |     |                                                                                                   |                             |            |                                                                                       |
|------------------|-------|-------|-----|---------------------------------------------------------------------------------------------------|-----------------------------|------------|---------------------------------------------------------------------------------------|
| CUSTOMER DRAWING |       |       |     |  深圳市莱联电子有限公司 |                             |            |                                                                                       |
| DRAWING          |       |       |     | SHENZHEN LAILIAN ELECTRONICS CO., LTD                                                             |                             |            |                                                                                       |
| CHECKED          |       |       |     |                                                                                                   |                             |            |                                                                                       |
| APPROVED         |       |       |     |                                                                                                   |                             |            |                                                                                       |
| TOLERANCES ARE   |       |       |     | TITLE                                                                                             | 排母 PIN距2.54 塑高8.5 双排10PIN直针 | REV.       | A                                                                                     |
| 30-150           | ±0.35 | ANGLE | ±3° | PART NO.                                                                                          | LAIL-PM2.54-6PX2-L          | UNITS      | mm                                                                                    |
| 10-30            | ±0.2  |       |     | DWG. NO.                                                                                          |                             | Projection |  |
| 5-10             | ±0.15 |       |     |                                                                                                   |                             |            |                                                                                       |
| 0-5              | ±0.1  |       |     |                                                                                                   |                             |            |                                                                                       |