





ROHS



PCB LAYOUT General±0.05mm.

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: 250V
Current Rating: 2AMP
Temperature Range: -40°Cto+105°C
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 500V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni

COSTOMTER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING			TITLEPIN距2.0 塑高2.0 双排4PIN直插REV.A			
CHECKED						
APPROVED						
TOLERANCES ARE			PART NO.LAIL-PZ2. 0-4PX2-LUNITSmm	DWG. NO.	Projection 	
30-150	±0.35	ANGLE				
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			±3°			