




ROHS



PCB LAYOUT General±0.05mm.

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: 250V

Current Rating: 3AMP

Temperature Range: -40°C to +105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 1000V


Material:

Insulator: Polyester (UL94V-0)

Standard: PA6T

Contact: Brass

Plating: Au over Ni



COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING					
CHECKED					
APPROVED					
TOLERANCES ARE		TITLE	排针 PIN距2.54 塑高2.5 单排3PIN直插	REV.	A
30-150	±0.35	PART NO.	LAIL-PZ2.54-3P-L	UNITS	mm
10-30	±0.2	DWG. NO.		Projection	
5-10	±0.15				
0-5	±0.1				