





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



PCB LAYOUT

SPECIFICATION:
Voltage Rating: AC 250V
Current Ratin : 1AMP
Temperature Range: -40°C~+105°C
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 500V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA9T
Contact: C5159
Plating: Au over Ni

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECKED					
APPROVED					
TOLERANCES ARE		TITLE	排母 PIN距1.27 塑高4.3 双排3PIN立贴	REV.	A
30-150	±0.35	PART NO.	LAIL-PM1.27-3PX2-T	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1	DWG. NO.		Projection	