





ROHS



PCB LAYOUT General±0.05mm.



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: 250V

Current Rating: 3AMP

Temperature Range: -40℃to+105℃

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage : AC 1000V

Material:

Insulator: Polyester (UL94V-0)

Standard: PA6T

Contact: Brass

Plating: Au over Ni

CUSTOMER DRAWING			LAILAN 深圳市莱联电子有限公司	
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD	
CHECKED				
APPROVED				
TOLERANCES ARE			TITLE	排针 PIN距2.54 塑高2.5 双排2PIN弯针
30-150	±0.35	ANGLE	PART NO.	LAIL-PZ2.54-2PX2-W
10-30	±0.2		UNITS	mm
5-10	±0.15		DWG. NO.	
0-5	±0.1		Projection	