





ROHS



PCB LAYOUT General±0.05mm.

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: 250V

Current Rating: 3AMP

Temperature Range: -40℃to+105℃

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 1000V

Material:

Insulator: Polyester (UL94V-0)

Standard: PA6T

Contact: Brass

Plating: Au over Ni

CUSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECKED					
APPROVED		TITLE	排针 PIN距2.54 塑高2.5 单排2PIN弯插	REV.	A
TOLERANCES ARE		PART NO.	LAIL-PZ2.54-2P-W	UNITS	mm
30-150	±0.35	ANGLE	DWG. NO.	Projection	
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				