


ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: 250V

Current Rating: 3AMP

Temperature Range: -40°C to $+105^{\circ}\text{C}$

Contact Resistance: $20\text{m}\Omega$ Max

Insulation Resistance: $1000\text{M}\Omega$ Min

Withstanding Voltage: AC 1000V


Material:

Insulator: Polyester (UL94V-0)

Standard: PA6T

Contact: Brass

Plating: Au over Ni



COSTOMER DRAWING			LAILAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED						
APPROVED						
TOLERANCES ARE			TITLE	排针 PIN距2.54 塑高2.5 双排2PIN立贴	REV.	A
30-150	± 0.35	ANGLE	PART NO.	LAIL-PZ2. 54-2PX2-T	UNITS	mm
10-30	± 0.2		DWG. NO.		Projection	
5-10	± 0.15					
0-5	± 0.1					